

# Tex-DIAPHRAGM

## NYLON-INSERTED DIAPHRAGM SHEET



### General Properties and Applications

Neoprene rubber with square woven 7.0 ounce nylon fabric for durability in dynamic applications requiring extra strength. Excellent stretch and tear resistance. Moderate oil resistance. Our exclusive post-cure process provides a smooth and clean finish free of talc, a must for PSA applications.

### Technical Data

Durometer	60 +/-5
Color	Black
Temperature Range	-30°F to +190°F
Fabric Type	7.0 ounce nylon
Continuous Lay Line	Includes style, durometer, and lot code
ASTM Line Call Out	D2000-M2-BC607-A14-B14-F17

Width (in.)	Gauge (in.)	Part Number	Ln Ft/ Roll	Sq Yds/ Roll	Fabric Plies	Lbs/ Roll
48"	1/16"	DIAP-2	100'	44.4	1	184
	1/8"	DIAP-4	100'	44.4	2	368
	3/16"	DIAP-6	50'	22.2	3	276
	1/4"	DIAP-8	50'	22.2	4	368

- ① Talc-free surface eliminates the need to clean the sheet rubber and is ideal for PSA applications.
- ① Certificates of Conformance indicating production date and lot code are available on request at the time of order.



#### Tex-TIP:

Check out the useful features on Texcel's newly engineered web site [www.texcelrubber.com](http://www.texcelrubber.com) today including Fractional Measurement Equivalents and an Industry Term Glossary.

